





## Product Brief — FP4209-C1 InstaTune Fast Random-Access Tunable Laser

#### **FEATURES**

Rapid arbitrary wavelength switching as fast as 2us/step User configurable look-up table (10k points across full tuning range) Compact, fully selfcontained module Interfaced via USB or fast (25MHz) SPI Logic output for synchronizing to sweep Programmable logic output for synchronizing to each wavelength step (sample window)

### **APPLICATIONS**

Test and Measurement
Fiber Sensing
Optical Communications

### **NOTES**

- Gap-free continuous wavelength tuning range centered about nominal wavelength
- Case temperature kept at 25°C
- Power variation across all wavelengths

### **OVERVIEW**

The FP4209 Fast Random-Access Tunable Laser (InstaTune) is a compact, self-contained tunable laser module capable of emitting any wavelength within the specified range and resolution available. Wavelength switching from any wavelength to any wavelength in as little as two microseconds while fully meeting specifications is supported. The module can be operated in scenarios where a host system is commanding wavelength changes as well as stand-alone where the module deterministically self-steps through a user defined sequence of wavelengths, thus generating an arbitrary waveform. Alternatively, the module can emit a programmable static wavelength. USB and SPI interfaces are provided for configuration and control. An evaluation board is also available.

## **SPECIFICATIONS**

General Parameter	Value	Unit
Center Wavelength	1550	nm
Tuning Range <sup>1</sup>	40	nm
Absolute Wavelength Accuracy	±15	pm
Wavelength Stability(24hr) <sup>2</sup>	±5	pm
Output Power	≥5	mW
Output Power Flatness <sup>3</sup>	±0.25	dB
Tuning Resolution	Tuning Range / 10k points	nm
SMSR	>30	dB
Wavelength Settling Time	<200	ns
Laser Linewidth	<50	MHz
Fiber Type	PM, Slow-axis aligned to key	
Fiber Connector	FC/ APC	
Case Temperature Operating Range	10°C - 55°C	Non- condensing
Case Temperature Storage Range	-10°C - 70°C	Non- condensing

As part of our policy of continuous product improvement, we reserve the right to change specifications at any time.







# Product Brief — FP4209-C1 InstaTune Fast Random-Access Tunable Laser

## **NOTES CONTINUED:**

- Maximum step rate when auto stepping, can dwell on any wavelength indefinitely
- Portion of step period required for wavelength settling
- Can be programmed in 10ns steps with the maximum width equal to the step period
- 7. Varies with case temperature (<100mA at 25°C)
- 8. Time to set new wavelength when in direct wavelength access mode using USB interface
- Time to set new wavelength when in direct wavelength access mode using Host SPI interface
- Time to set new wavelength when in direct wavelength access mode using DAC SPI interface

Sweeping Parameter	Value	Unit
Number Wavelength Steps (min)	1	
Number Wavelength Steps (max)	10000	
Wavelength Step Period (min)	2	us
Wavelength Step Period (max) <sup>4</sup>	655.35	us
Wavelength Settling Time <sup>5</sup>	<200	ns
SweepSync Timing	Active-low pulse generated at the beginning of the specified wavelength sequence	
StepSync Timing <sup>6</sup>	Active-low pulse generated every laser wavelength step.	

Electrical Parameter	Value	Unit
Power		
3.3V Supply Current	200	mA
3.8V Supply Current	1000	mA
5.0V Supply Current <sup>7</sup>	1500	mA
Communication		
Host USB Command <sup>8</sup>	≤1	ms
Host SPI Command <sup>9</sup>	<4	us
DAC SPI Command <sup>10</sup>	<4	us



As part of our policy of continuous product improvement, we reserve the right to change specifications at any time.







# Product Brief — FP4209-C1 InstaTune Fast Random-Access Tunable Laser

## **NOTES CONTINUED:**

- Pin connections that have the same name are shorted inside the module
- 12. Direct SPI communication for quick wavelength index switching to any of the 10000 points in the LUT. SPI for DAC index communication. First bit is laser enable 1/ disable 0, followed by integer from 0 to 9999.
- 13. External digital signals
  SweepSync and StepSync
  may be used to monitor
  the sweep operations of
  the InstaTune using
  external hardware. The
  digital interface consists of
  two output signals whose
  function is configurable in
  the register settings.

## **PIN ASSIGNMENTS**

10 Pin Header					
Pin Name	Pin#	Pin#	Pin Name		
VISRC	1	2	VISRC		
ISRCGND	3	4	ISRCGND		
NC	5	6	NC		
PGND	7	8	PGND		
VTEC	9	10	VTEC		

30 Pin Header					
Pin Name	Pin#	Pin#	Pin Name		
DAC FC1 SSELO	1	2	DAC FC1 MOSI		
DAC DC1 SCLK	3	4	DAC FC1 MISO		
DAC USB DP R	5	6	DAC USB DM R		
DAC USB VBUS R	7	8	DAC Trig In		
DAC Sweep Sync	9	10	DAC Step Sync		
DGND	11	12	DGND		
VD3R3	13	14	VD3R3		
AGND	15	16	AGND		
VA3R3	17	18	VA3R3		
Host Alarm	19	20	Host Laser Enable		
Host Laser Valid	21	22	Host Mod Valid		
Host USB VBUS_R	23	24	DGND		
Host USB DP R	25	26	Host USB DM R		
Host SCLK	27	28	Host MISO		
Host SSELO	29	30	Host MOSI		